Technical Data

Phot **O**centric



Daylight Precision Durable

FEATURES

Photocentric's new tough and durable photopolymer formulation is ideal for making strong but slightly flexible objects. DL Precision Durable is ideal for 3d printing durable, strong objects that can be bent without breaking. Thick objects are stiff but can be made to bend and flex under strain and will return to their original shape. DL Precision Durable can be used for the fabrication of functional parts requiring a higher impact strength and durability.

DL Precision Durable provides excellent imaging in your Liquid Crystal machines. You will experience the benefits of fast exposure times and a wide exposure latitude, allowing you to hold the finest details your machine can provide. The solid material is tough, durable and long lasting provided it is stored in dry conditions away from strong UV light.

PROCESSING INSTRUCTIONS

Follow the procedures laid out in your 3D Liquid Crystal user manual.

For best post-processing results, clean using a Photocentric Wash 15L with Photocentric Resin Cleaner for maximum 15 minutes. Rinse thoroughly with warm to hot water. Place in Cure M or L2 for 1-2 hours at 60-80°C. Durable parts will seem flexible while in heat, once cooled they display the desired properties of the material. If still tacky, place in water and UV for 20 minutes

DATA

DAIA	
Viscosity (At 25°C Brookfield spindle 3)	1200 cPs
Hardness ASTM D2240 (After post exposure for 60 minutes at 60°C)	60 Shore D
Tensile strength ASTM D638 (After post exposure for 60 minutes at 60°C)	42 MPa
Elongation at break ASTM D638 (After post exposure)	14%
Young's modulus ASTM D638 (After post exposure for 60 minutes at 60°C)	1570 MPa
Impact strength notched Izod ASTM D256 (After post exposure)	14 kJ/m2
Flexural strength ASTM D792 (After post exposure)	28 MPa
Flexural modulus ASTM D792 (After post exposure)	760 MPa
Water absorption (24 h at 60°C)	0.9 wt%
Heat deflection temperature Storage Density	75°C 10 <t>50°C 1.09 g/cm3</t>

AVAILABLE COLOURS

Black.

Available in 1kg bottles.

UK Photocentric Ltd. Cambridge House, Oxney Rd, Peterborough, PE1 5YW email: info@photocentric.co.uk USA Photocentric Inc. 2205 West Parkside Lane, Phoenix, 85027, AZ email: info@photocentricusa.com www.photocentricgroup.com



